



Ciljna grupa

Idealno rješenje za korisnike desktop računara kao i prostor oko radnog stola. Starosna dob 45+.

Napomena: Strogo je zabranjena upotreba ove vrste leće u saobraćaju.

Tehnologija

OPTOTECH OFFICE 10

Način izrade

Unutrašnja izrada digresivne površine.

Poručivanje dioptrija

1/4

Progresivna dužina

18 mm

Način poručivanja

RX podaci za dioptriju na blizinu

Selekcija dizajna:

- Tip A do 50 godina starosti

- Tip B preko 50 godina starosti

Koristiti razmak zjenica za daljinu,

po mogućnosti za svako oko

pojedinačno (IPD)

Minimalna visina ugradnje

20 mm

Optimizacija

Specijalno tanjenje za leću u plus opsegu na osnovu oblika okvira i parametra za fitovanje leće u okvir. Ukoliko se leća poručuje bez opcije Optimizacija, topografija leće će biti decentrirana nazalno u odnosu na geometrijski centar za 2,5 mm.

Ocjene korisnika

Vid – daljina



Vid – blizina



Spontano privikavanje



Vid – srednja daljina



Komfor pri korištenju




Korištenje digitalnih uređaja



Oznake na lećama

■ gravure
■ markeri



MATERIJALI

1.50 CR-39	1
1.53 Trivex	2
1.56 Mid. index	3
1.59 Poly	4
1.60 High Index	5
1.60 Tribrid	6
1.67 High Index	7
1.74 High Index	8

DORADE

Bez dorade	W	Transitions GEN 8 Sapphire	F	Nupolar Gray	S
Remuve 400	H	Transitions GEN 8 Amethyst	M	Nupolar Gray Light	L
Remuve 420	R	Transitions GEN 8 Amber	A	Nupolar Green	E
Remuve 420 Photomatic Brown	O	Transitions GEN 8 Emerald	E	Transitions XTRActive Polarised Gray	X
Remuve 420 Photomatic Gray	U	Transitions XTRActive Brown	C	Photomatic Brown	B
Transitions GEN 8 Brown	Z	Transitions XTRActive Gray	L	Photomatic Gray	I
Transitions GEN 8 Gray	N	Transitions XTRActive Green	K	DriveWear	D
Transitions GEN 8 Green	V	Nupolar Brown	B		