

MONOFOKAL

# LIGHTFORM2.0



## Ciljna grupa

Monofokalna leća sa blago pojačanim dodatkom u donjem dijelu leće. Preporučuje se kategoriji ljudi koji osjećaju napor u očima, tenziju kao i glavobolju usljed dužeg rada sa digitalnim uređajima.

Dizajn 0.40 – starosna dob 20+  
Dizajn 0.60 – starosna dob 35+  
Dizajn 0.80 – starosna dob 43+

## Tehnologija

IOT Endless Anti-fatigue SV

## Način izrade

Unutrašnja izrada monofokalne površine.

## Poručivanje dioptrija

1/4, 1/8, 1/100

## Individualni parametri

IPD, Vertex, Panto, Ztilt

## Minimalna visina ugradnje

16 mm

## Optimizacija

Specijalno tanjenje za leću u plus opsegu na osnovu oblika okvira i parametra za fitovanje leće u okvir. Ukoliko se leća poručuje bez opcije Optimizacija, topografija leće će biti decentrirana nazalno u odnosu na geometrijski centar za 2,5 mm.

## Ocjene korisnika

Vid – daljina



Vid – blizina



Spontano privikavanje



Vid – srednja daljina



Komfor pri korištenju




Korištenje digitalnih uređaja



## Oznake na lećama

▬ gravure  
▬ markeri



## MATERIJALI

1.50 CR-39	1
1.53 Trivex	2
1.59 Poly	4
1.60 High Index	5
1.60 Tribrid	6
1.67 High Index	7
1.74 High Index	8

## DORADE

Bez dorade	W	Transitions GEN 8 Sapphire	F	Nupolar Gray	S
Remuve 400	H	Transitions GEN 8 Amethyst	M	Nupolar Gray Light	L
Remuve 420	R	Transitions GEN 8 Amber	A	Nupolar Green	E
Remuve 420 Photomatic Brown	O	Transitions GEN 8 Emerald	E	Transitions XTRActive Polarised Gray	X
Remuve 420 Photomatic Gray	U	Transitions XTRActive Brown	C	DriveWear	D
Transitions GEN 8 Brown	Z	Transitions XTRActive Gray	L		
Transitions GEN 8 Gray	N	Transitions XTRActive Green	K		
Transitions GEN 8 Green	V	Nupolar Brown	B		